

Crisp Fall Savings Are Here!

Instant Rebates UP TO \$395



MY INTELLIGENCE
MIGHT BE ARTIFICIAL,
BUT THESE REBATES
ARE THE REAL THING!

Promotion valid **10/1/24 - 12/31/24**

UPS Systems

Product	Rebate	Description
Tripp Lite Series Cloud-Connected UPS System		
AVR750UNC	\$12.00	750VA 450W Line-Interactive Cloud-Connected UPS with Remote Monitoring
Tripp Lite series SmartOnline Double-Conversion UPS System		
SU2200XLCD	\$114.57	1960VA 1770W, 7 Outlets, Extended Run, Network Card Option, LCD, Tower
Eaton Double-Conversion Extended-Run UPS System		
9SX1500G	\$166.22	9SX 1500VA 1350W, 208V, 6 C13 Outlets, Cybersecure Network Card Option, Tower



Power Distribution Units (PDUs)

Basic PDU		
EVBA609X-E	\$146.25	Rack PDU G4, 0U, 200-415V, 5-23kW, 16-55A, 24 C13 and 18 C39 Outlets, Universal End Entry Input
Metered Input PDUs		
EVM14609X	\$266.27	3-Phase Rack PDU G4, 0U, 208V, 17.3kW, 48A, 24 C13 and 18 C39 Outlets, 460P9W Input, 10 ft. Cord
EVM14609X-06	\$266.27	3-Phase Rack PDU G4, 0U, 208V, 17.3kW, 48A, 24 C13 and 18 C39 Outlets, 460P9W Input, 6 ft. Cord
EVMIG332X	\$194.51	3-Phase Rack PDU G4, 0U, 240/415V, 17.3kW, 32A, 24 C13 and 18 C39 Outlets, 532P6W Input, 10 ft. Cord
EVMIGU23A-E	\$185.25	Universal-Input Rack PDU G4, 0U, 208V and 415/240V, 12 C13 and 12 C39 Outlets, Input Cable Sold Separately
EVMIGU23X-E	\$229.13	Universal-Input Rack PDU G4, 0U, 208V and 415/240V, 24 C13 and 18 C39 Outlets, Input End Entry, Input Cable Sold Separately
Managed PDUs		
EVMA4609X	\$345.05	3-Phase Rack PDU G4, 0U, 208V, 17.3kW, 48A, 24 C13 and 18 C39 Outlets, 460P9W Input, 10 ft. Cord
EVMA4609X-06	\$340.18	3-Phase Rack PDU G4, 0U, 208V, 17.3kW, 48A, 24 C13 and 18 C39 Outlets, 460P9W Input, 6 ft. Cord
EVMAG332X	\$259.35	3-Phase Rack PDU G4, 0U, 240/415V, 17.3kW, 32A, 24 C13 and 18 C39 Outlets, 532P6W input, 10 ft. Cord
EVMAGU23A-E	\$243.65	Universal Input Rack PDU G4, 0U, 208V and 415/240V, 12 C13 and 12 C39 Outlets, Input Cable Sold Separately
EVMAGU23X-E	\$286.16	Universal Input Rack PDU G4, 0U, 208V and 415/240V, 24 C13 and 18 C39 Outlets, Input Cable Sold Separately



Isolation Transformer

Product	Rebate	Description
ISS00	\$107.17	500W Isolation Transformer-Based Power Conditioner, 4 Outlets, TAA



Rebates apply only to items in stock during the promotional period. Excludes CDW, Amazon (US & Canada), Provantage and Staples.

Power Strips

Product	Rebate	Description
Power Strips for Home/Office		
PS222DATAM	\$8.72	2-Outlet In-Desk Power and Charging Dock, 4x USB-A, USB-B, HDMI, RJ11, RJ45, Antimicrobial Protection, Black, 10 ft. (3 m) Cord
PS22POPAM	\$6.16	2-Outlet Pop-Up Power and Charging Dock, 2x USB-A, Antimicrobial Protection, Black, 6 ft. (1.8 m) Cord
PS240406	\$10.11	4 Outlets, 24 in. Housing, 6 ft. (1.83 m) Cord
Power Strips for Healthcare Applications		
PS-402-HG-OEMLM	\$9.09	Safe-IT UL 1363A Medical-Grade Power Strip for Patient Care Vicinities, 4 Hospital-Grade Outlets, Load Monitor, Safety Covers, Antimicrobial, 2 ft. (0.6 m) Cord
PS-415-HG-OEMLM	\$9.54	Safe-IT UL 1363A Medical-Grade Power Strip for Patient Care Vicinities, 4 Hospital-Grade Outlets, Load Monitor, Safety Covers, Antimicrobial, 15 ft. (4.6 m) Cord
PS-415-HGUSB	\$7.11	Safe-IT UL 1363 Medical-Grade Power Strip, 4 Hospital-Grade Outlets, USB Charging, Safety Covers, Antimicrobial, 15 ft. (4.6 m) Cord
PS-602-HGUSB	\$6.74	Safe-IT UL 1363 Medical-Grade Power Strip, 6 Hospital-Grade Outlets, USB Charging, Safety Covers, Antimicrobial, 2 ft. (4.6 m) Cord
PS-606-HGUSB	\$8.17	Safe-IT UL 1363 Medical-Grade Power Strip, 6 Hospital-Grade Outlets, USB Charging, Safety Covers, Antimicrobial, 6 ft. (1.8 m) Cord
PS-607-HG-OEMLM	\$9.99	Safe-IT UL 1363A Medical-Grade Power Strip for Patient Care Vicinities, 6 Hospital-Grade Outlets, Load Monitor, Safety Covers, Antimicrobial, 7 ft. (2.1 m) Cord
PS-615-HG-OEMLM	\$10.00	Safe-IT UL 1363A Medical-Grade Power Strip for Patient Care Vicinities, 6 Hospital-Grade Outlets, Load Monitor, Safety Covers, Antimicrobial, 15 ft. (4.6 m) Cord
PS-615-HGUSB	\$8.58	Safe-IT UL 1363 Medical-Grade Power Strip, 6 Hospital-Grade Outlets, USB Charging, Safety Covers, Antimicrobial, 15 ft. (4.6 m) Cord



Power Strips

Product	Rebate	Description
TLM210CAM	\$97.34	Safe-IT 6-Port USB Charging Station, 2x USB-C 60W, 4x USB-A, 2x 5-15R, Wireless Charging, 1000 Joules, Antimicrobial, 10 ft. (3 m) Cord
TLM610CPAM	\$114.00	Safe-IT 5-Port Mobile Power Tower/USB Charging Station, USB-C 60W, 4x USB-A, 6x 5-15R, Wireless Charging, 1000 Joules, Antimicrobial, 10 ft. (3 m) Cord
TLP12POAM	\$5.82	In-Desktop Power Grommet, 1x 5-15R, 2x USB-A Charging, Surge Protection, Antimicrobial, 10 ft. (3 m) Cord, Black
TLP410UCUF0AM	\$6.71	Safe-IT Conference Power Surge Protector, 4x Rotating 5-15R Outlets, USB-C & 3 USB-A Ports, Antimicrobial, 10 ft. (3 m) Cord
TLP610COILAM	\$8.13	Safe-IT Surge Protector, 6x 5-15R, 300 Joules, Antimicrobial, 10 ft. (3 m) Coiled Cord, Black



KVM Switches

Product	Rebate	Description
B022-U16-IP	\$78.24	NetDirector 16-Port 1U Rack-Mount IP KVM Switch, TAA
B024-H4U16	\$161.25	16-Port 1U Rack-Mount KVM Switch, 4K 60 Hz Video/Audio, USB Peripheral Sharing
B064C-16-1-IP	\$156.00	16-Port 1U Cat5 KVM over IP Switch, 19 in. LCD, 1920 x 1200 60 Hz, TAA
B064C-16-1X1-IP	\$256.00	16-Port 1U Cat5 KVM over IP Switch, 9 in. LCD, Virtual Media, 1920 x 1200 60 Hz



TRIPP-LITE
by **EATON**

For more information, contact:

TDSYNNEX@eaton.com
se Eaton@tdsynnex.com
tripplite@tdsynnex.com



Tripp Lite is now part of Eaton.

© 2024 Eaton. All rights reserved.

Device Charging

Product	Rebate	Description
Charging Towers		
CST16AC	\$157.76	16-Device AC Charging Tower for Chromebooks, Open Frame, White
CST20AC	\$186.20	20-Device AC Charging Tower for Chromebooks, Open Frame, White
CST32AC	\$348.40	16-Device AC Charging Tower for Chromebooks, Open Frame, White, 2-Pack (32 Devices Total)
CST40AC	\$395.40	20-Device AC Charging Tower for Chromebooks, Open Frame, White, 2-Pack (40 Devices Total)
Power Bank		
UPB-04K0-1CM	\$3.84	Portable Wireless Magnetic Charging Power Bank, USB-C Output, 18W, 4000mAh, Lithium-Ion, Black
Charging Cables		
M100-006-WH	\$1.93	USB-A to Lightning Sync/Charge Cable, M/M, MFI Certified, White, 6 ft. (1.8 m)
Car Charger		
U280-C03-36W-1B	\$2.32	3-Port USB Car Charger, USB-C PD 3.0 up to 18W, 2 USB-A QC 3.0 up to 36W
Wall Charger		
U280-W01-18C1-K	\$2.50	USB-C Wall Charger with USB-C to Lightning Cable - 18W PD Charging, GaN Technology

Connectivity

Product	Rebate	Description
USB-C Docking Stations		
U442-DOCK10-S	\$3.48	4K HDMI, USB 3.x (5Gbps), USB-A Hub, Memory Card, 60W PD Charging
U442-DOCK12-S	\$4.35	Triple Display, HDMI, VGA, USB 3.x (5Gbps), USB-A Hub, 60W PD Charging
U442-DOCK17-GY	\$4.35	Optional Internal Hard Drive, 4K HDMI, USB 3.x (5Gbps), USB-A/USB-C Hub, SATA III, 100W PD Charging
U442-DOCK3-B	\$5.08	4K HDMI, VGA, USB 3.x (5Gbps), USB-A/C Hub, Gigabit Ethernet, Memory Card Slots, 100W PD Charging
U442-DOCK5-GY	\$5.08	4K HDMI, USB 3.x (5Gbps), USB-A/C Hub Ports, GbE, Memory Card, 100W PD Charging
U442-DOCK1	\$7.25	Dual Display, 4K HDMI/mDP, VGA, USB 3.x (5Gbps), USB-A/C Hub, GbE, Memory Card, 100W PD Charging
U442-DOCK1-B	\$7.25	Dual Display, 4K HDMI, mDP, VGA, USB 3.x (5Gbps), USB-A/C Hub, GbE, Memory Card, 100W PD Charging
U442-DOCK2-S	\$7.54	Dual Display, 4K HDMI, mDP, VGA, USB 3.x (5Gbps), USB-A/C Hub, GbE, 60W PD Charging
U442-DOCK40-6	\$8.40	Mini Dock and Multiport Adapter - 8K HDMI, USB 3.x Gen 2 (10Gbps) Hub Ports, HDR, HDCP 2.3, Gigabit Ethernet, 100W PD Charging
U442AB-DOCK9	\$16.80	Safe-IT USB-C Dock, Triple Display - 4K 60 Hz HDMI/DisplayPort, VGA, USB 3.2 Gen 2, USB Hub, Gigabit Ethernet, 100W PD Charging, Antibacterial

Product	Rebate	Description
AV Cables & Adapters		
P568FM-10M-8K6	\$15.00	8K HDMI Fiber Active Optical Cable, 8K UHD 60 Hz, HDR, Detachable Connector, M/M, Black, 33 ft. (10 m)
P568FM-20M-8K6	\$16.20	8K HDMI Fiber Active Optical Cable, 8K UHD 60 Hz, HDR, Detachable Connector, M/M, Black, 66 ft. (20 m)
P568FM-30M-8K6	\$17.40	8K HDMI Fiber Active Optical Cable, 8K UHD 60 Hz, HDR, Detachable Connector, M/M, Black, 98 ft. (30 m)
P568FM-40M-8K6	\$18.60	8K HDMI Fiber Active Optical Cable, 8K UHD 60 Hz, HDR, Detachable Connector, M/M, Black, 131 ft. (40 m)
P579-009-8K6	\$8.17	DisplayPort Extension Cable with Active Repeater and Latching Connector (M/F), 8K 60 Hz, HDR, 4:4:4, HDCP 2.2, 9 ft. (2.7 m), TAA
P580-003-8K6-2	\$1.56	DisplayPort 2.1 Cable with Latching Connectors (M/M), 8K 60 Hz, 40 Gbps, HDR, HBR3, MST, 4:4:4, HDCP 2.2, Black, 3 ft. (0.9 m)
P580-006-8K6-2	\$1.80	DisplayPort 2.1 Cable with Latching Connectors (M/M), 8K 60 Hz, 40 Gbps, HDR, HBR3, MST, 4:4:4, HDCP 2.2, Black, 6 ft. (1.8 m)
P131-06N	\$1.97	HDMI to VGA with Audio Converter Cable Adapter (M/F), 6 in. (15.24 cm), TAA
P316-06N	\$0.23	3.5 mm Mini Stereo to RCA Audio Y Splitter Adapter Cable (F/2xM), 6 in. (15.2 cm)
A102-02M	\$0.68	Toslink Digital Optical SPDIF Audio Cable, Black, 6.56 ft. (2 M)
U261-001-BT5	\$2.48	Mini Bluetooth 5.0 USB Adapter

Product	Rebate	Description
Network Cables		
N820-01M	\$1.00	10Gb Duplex Multimode 50/125 OM3 OFNP Fiber Patch Cable (LC/LC), Aqua, 3.3 ft. (1m)
N820-01M-TAA	\$1.58	10Gb Duplex Multimode 50/125 OM3 OFNP Fiber Patch Cable (LC/LC), Aqua, 3.3 ft. (1m), TAA
N820-02M-TAA	\$1.74	10Gb Duplex Multimode 50/125 OM3 OFNP Fiber Patch Cable (LC/LC), Aqua, 6.6 ft. (2 m), TAA
N820-03M-TAA	\$1.86	10Gb Duplex Multimode 50/125 OM3 OFNP Fiber Patch Cable (LC/LC), Aqua, 9.8 ft. (3 m), TAA
N820-06M	\$1.48	10Gb Duplex Multimode 50/125 OM3 OFNP Fiber Patch Cable (LC/LC), Aqua, 19.7 ft. (6 m)
N820X-01M	\$1.26	400G Multimode 50/125 OM3 Switchable Fiber Optic Cable (Duplex LC-PC M/M), LSZH, Aqua, 3.3 ft. (1 m)
N820X-02M	\$1.37	400G Multimode 50/125 OM3 Switchable Fiber Optic Cable (Duplex LC-PC M/M), LSZH, Aqua, 6.6 ft. (2 m)
N820X-03M	\$1.48	400G Multimode 50/125 OM3 Switchable Fiber Optic Cable (Duplex LC-PC M/M), LSZH, Aqua, 9.8 ft. (3 m)
N820X-04M	\$1.56	400G Multimode 50/125 OM3 Switchable Fiber Optic Cable (Duplex LC-PC M/M), LSZH, Aqua, 13.1 ft. (4 m)
N820X-05M	\$1.65	400G Multimode 50/125 OM3 Switchable Fiber Optic Cable (Duplex LC-PC M/M), LSZH, Aqua, 16.4 ft. (5 m)

Product	Rebate	Description
Adapter Cables		
U444-003-DP	\$2.48	USB-C to DisplayPort Active Adapter Cable (M/M), 4K 60 Hz, 3 ft. (0.9 m)
U444-006-HWE	\$2.61	USB-C to HDMI Adapter Cable (M/M), 4K, 4:4:4, Thunderbolt 3 Compatible, White, 6 ft. (1.8 m)
U444-06N-HDV4K	\$3.48	USB-C Multiport Adapter (M/3xF) 4K HDMI, DVI, VGA, HDCP, White
AV Extenders		
B127-1A1-WHD3	\$34.40	HDMI over Wireless Extender Kit w IR, 4K 60 Hz, Wireless HDMI, Switchable Channel, Up to 164 ft. (50 m)
B127-1A1-WHD4HH	\$27.20	HDMI over Wireless Extender Kit, 4K 60 Hz, Wireless HDMI, Switchable Channel, Up to 65 ft. (20 m)
B127A-111-BHTH	\$28.96	HDMI over Cat6 Extender Kit, Transmitter and Receiver with Repeater, 4K 60Hz, 4:4:4, IR, HDR, PoC, 230 ft., (70.1 m), TAA
B127U-111-PHPH	\$19.80	HDMI over Cat6 Extender Kit, Pigtail Transmitter/Receiver, 4K 60 Hz, HDR, 4:4:4, 230 ft. (70.1 m), TAA
B127U-002-PHPH2	\$26.40	HDMI over Cat6 Extender Kit, Pigtail Transmitter/2x Receivers, 4K 60 Hz, HDR, 4:4:4, 230 ft. (70.1 m), TAA
B127U-002-PDPD2	\$37.20	DisplayPort over Cat6 Extender Kit, Pigtail Transmitter/2x Receivers, 4K 60 Hz, HDR, 4:4:4, 230 ft. (70.1 m), TAA
B127U-002-PDPH2	\$30.00	2-Port DisplayPort to HDMI over Cat6 Extender Kit, Pigtail Transmitter/2x Receivers, 4K 60 Hz, HDR, 4:4:4, 230 ft. (70.1 m), TAA
B127U-111-PDPD	\$26.40	DisplayPort over Cat6 Extender Kit, Pigtail Transmitter/Receiver, 4K 60 Hz, HDR, 4:4:4, 230 ft. (70.1 m), TAA
BHD8T3-TRX2	\$158.40	HDBaseT 3.0 Transmitter and Receiver Kit, HDMI 4K 60 Hz (4:4:4), RS-232, IR Control, Up to 328 ft. (100 m), TAA

Product	Rebate	Description
Industrial Ethernet Switches		
NGI-M08C4-L2	\$48.75	8-Port Managed Industrial Gigabit Ethernet Switch, Layer 2, 10/100/1000 Mbps, 4 GbE SFP Ports, DIN Mount, TAA
NGI-U08A	\$16.75	8-Port Unmanaged Industrial Gigabit Ethernet Switch, 10/100/1000 Mbps, Ruggedized, EIP QoS, DIN Mount, TAA

Display Mounts/Carts

Product	Rebate	Description
Rolling Carts		
DMCS3270XP	\$40.99	Rolling TV/Monitor Cart for 32" to 70" Flat/Curved Displays
DMCS3770ROT	\$33.50	Rolling TV/Monitor Cart for 37" to 70" Flat-Screen Displays, Rotating Portrait/Landscape Mount
DMCS60100XX	\$51.25	Heavy-Duty Rolling TV Cart for 60" to 100" Displays, Height-Adjustable
DMCS60100XCK	\$72.75	Safe-IT Heavy-Duty Rolling TV Cart for 60" to 100" Displays, Height-Adjustable, Crank Handle, Antimicrobial Protection
DMCS70120AMUL	\$69.24	Safe-IT Heavy-Duty Rolling Cart for 70" to 120" Displays, UL Certified, Antimicrobial Protection
DMCS4560HDS	\$34.61	Heavy-Duty Streamline Portrait Mobile Cart for 45" to 60" Flat-Panel Displays

Product	Rebate	Description
Desktop Mounts		
DDR1732NBMTAA	\$24.00	Full-Motion Desktop Clamp for Laptop and 17" to 32" Monitor, Aluminum, TAA
DDR811TRAYTAA	\$4.32	3-Tray Document Holder with Desktop Clamp, TAA

Product	Rebate	Description
Monitor Stand		
DDVD1727AM	\$10.58	Safe-IT Adjustable Monitor Stand for 17" to 27" Displays, Antimicrobial

Product	Rebate	Description
Wall Mounts		
DWMS070HD	\$70.13	Height-Adjustable Mount for 50" to 70" Flat-Panel Interactive Displays
DWMSCL4570W	\$39.98	Pop-Out Security Mount with Combination Lock for 45" to 70" TVs and Monitors, Landscape
DWMSCP4570W	\$39.98	Pop-Out Security TV Wall Mount with Combination Lock for 45" to 70" Televisions and Monitors, Portrait

Product	Rebate	Description
Workstations		
WWSS1332C	\$70.98	WorkWise Desk-Mounted Workstation, Single Display
WWSS1DWSTAA	\$68.85	Mobile Workstation with Monitor Arm, Casters, Locking Drawer, TAA
WWSS2DWSTAA	\$76.30	Mobile Workstation with 2x Adjustable Shelves, 2x Metal Drawers, Locking Casters, TAA
WWSSC2414TAA	\$7.89	Desk-Clamp Monitor Riser with Storage Drawer, TAA
WWSSC0526AM	\$5.67	Safe-IT Clamp-On Monitor Riser, Antimicrobial Protection, 25.6 in. (65 cm)
WWSSC0540AM	\$6.97	Safe-IT Clamp-On Monitor Riser, Antimicrobial Protection, 39.4 in. (100 cm)
WWSSD3622	\$27.59	Height-Adjustable Sit-Stand Desktop Workstation
WWSSDC	\$68.16	Sit-Stand Workstation, Clamp-on
WWSSDTAM	\$18.16	Safe-IT Adjustable-Height Sit-Stand Desktop Workstation, Antimicrobial Protection
WWSSDFSAM	\$12.02	Safe-IT Adjustable-Height Wall-Mount Workstation, Antimicrobial Protection
WWSSRC	\$18.16	Rolling Desk TV/Monitor Cart, Height Adjustable
WWSSRSTAA	\$57.70	Mobile Workstation with Adjustable Shelves, Locking Casters, TAA

Rebates apply only to items in stock during the promotional period. Excludes CDW, Amazon (US & Canada), Provantage and Staples.

TRIPP-LITE
by **EATON**

Tripp Lite is now part of Eaton.

For more information, contact:

TDSYNEX@eaton.com
seeaton@tdsynnex.com
tripplite@tdsynnex.com

© 2024 Eaton. All rights reserved.

TD SYNEX

24-09-111